

**WNMG indexable insert for finishing 30 pieces, HB7120-1, Size: 080408****Order data**

Order number	GG2976 080408
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Cutting depth $a_{p \max}$	2.75 mm
Main application	M
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.1 - 0.4 mm/rev.
Cutting speed v_c main application	90 - 290 mm/min
Number of changes/inserts	6
Contents	251964 HB7120-1
Finishing/roughing assignment	Finishing
ISO code indexable insert	WNMG 080408
Cutting depth a_p	0.3 - 2 mm
Corner radius	0.8 mm
Quantity	30
Type	HB7120-1

Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2976 080408