

Garant
VB.T 160408, Grade: HB7120-1


Order data

Order number	261234 HB7120-1
GTIN	4045197818850
Item class	21G

Description

VB.T 160408 HB7120-1 Grade: HB7120-1
 Chip breaker: VM
 Tolerance: M
 Cutting depth a_p : 0.5 - 2.5 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 80 - 260 m/min

Technical description

Cutting speed v_c main application	80 - 260 m/min
Corner radius	0.8 mm
Main application	M
Grade	HB7120-1
Feed f	0.1 - 0.4 mm/rev.
Chip breaker	VM

Cutting conditions	continuous
Cutting depth a_p	0.5 - 2.5 mm
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	VBMT 160408
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning