

**TCMT indexable insert for finishing 50 pieces, HB7140-2, Size: 110202****Order data**

Order number	GG3545 110202
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Cutting depth $a_{p \max}$	2.75 mm
Corner radius	0.2 mm
Cutting speed v_c main application	70 - 230 mm/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
Feed f	0.1 - 0.3 mm/rev.
Number of changes/inserts	3
ISO code indexable insert	TCMT 110202
Cutting depth $a_{p \min}$	0.15 mm
Main application	M
Contents	260950 HB7140-2
Coating	coated

Data sheet

Quantity	50
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3545 110202