

Garant**WNMG indexable insert for finishing 30 pieces, HB7140-2, Size: 080404****Order data**

Order number	GG2978 080404
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.1 - 0.4 mm/rev.
Quantity	30
Cutting depth a_p	0.3 - 2 mm
Number of changes/inserts	6
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	2.75 mm
Finishing/roughing assignment	Finishing
Main application	M
Coating	coated
Contents	251962 HB7140-2
ISO code indexable insert	WNMG 080404
Tool material	Carbide
Corner radius	0.4 mm
Cutting speed v_c main application	70 - 230 mm/min

Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2978 080404