

Garant**CC.T 09T302, Grade: HB7140-1**

Order data

Order number	260056 HB7140-1
GTIN	4045197818966
Item class	21G

Description

CCMT 09T302 HB7140-1 Grade: HB7140-1
Chip breaker: VS
Tolerance: M
Cutting depth a_p : 0.2 - 2.5 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 70 - 260 m/min

Technical description

Cutting conditions	slightly interrupted
Grade	HB7140-1
Feed f	0.1 - 0.3 mm/rev.
Chip breaker	VS
Main application	M
Corner radius	0.2 mm

Cutting speed v_c main application	70 - 260 m/min
Cutting depth a_p	0.2 - 2.5 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 09T302
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning