

Garant**WNMG indexable insert for finishing 30 pieces, HB7140-2, Size: 080408****Order data**

Order number	GG2978 080408
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	6
Quantity	30
Feed f	0.1 - 0.4 mm/rev.
Cutting depth $a_{p \max}$	2.75 mm
Corner radius	0.8 mm
Cutting speed v_c main application	70 - 230 mm/min
Contents	251964 HB7140-2
ISO code indexable insert	WNMG 080408
Coating	coated
Cutting depth a_p	0.3 - 2 mm
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.55 mm
Main application	M
Tool material	Carbide

Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2978 080408