

Garant**TCMT indexable insert for medium machining 30 pieces, HB7120-1, Size: 110204****Order data**

Order number	GG3546 110204
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	2.75 mm
Tolerance	M
Cutting speed v_c main application	80 - 260 mm/min
Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	3
Corner radius	0.4 mm
Cutting depth a_p	0.5 - 2.5 mm
ISO code indexable insert	TCMT 110204
Tool material	Carbide
Main application	M
Contents	260982 HB7120-1

Quantity	30
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3546 110204