



TCMT indexable insert for medium machining 30 pieces, HB7130-2, Size: 16T308



Order data

Order number	GG3547 16T308
GTIN	4067263096917
Item class	GGN

Technical description

Number of changes/inserts	3
ISO code indexable insert	TCMT 16T308
Cutting depth $a_{p \max}$	4 mm
Main application	M
Cutting speed v_c main application	70 - 240 mm/min
Feed f	0.1 - 0.4 mm/rev.
Cutting depth a_p	0.5 - 2.5 mm
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
Tolerance	M
Tool material	Carbide
Cutting depth $a_{p \min}$	0.55 mm
Contents	260988 HB7130-2
Quantity	30

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3547 16T308