

Garant
SCMT 09T308, Grade: HB7140-1


Order data

Order number	260744 HB7140-1
GTIN	4045197819215
Item class	21G

Description

SCMT 09T308 HB7140-1 Corner radius: 0.8 mm
 Grade: HB7140-1
 Chip breaker: VS
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 70 - 260 m/min

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Corner radius	0.8 mm
Cutting speed v_c main application	70 - 260 m/min
Feed f	0.1 - 0.3 mm/rev.
Cutting conditions	slightly interrupted
Chip breaker	VS
Grade	HB7140-1

Main application	M
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	SCMT 09T308
Number of changes/inserts	4
Type of product	Indexable insert for turning