


VBMT indexable insert for finishing 30 pieces, HB7130-2, Size: 110304

Order data

Order number	GG3553 110304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	80 - 270 mm/min
Number of changes/inserts	2
Feed f	0.1 - 0.3 mm/rev.
Main application	M
Cutting depth a_p	0.2 - 1.5 mm
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
ISO code indexable insert	VBMT 110304
Contents	261144 HB7130-2
Cutting depth $a_{p \max}$	1.75 mm
Tool material	Carbide
Quantity	30
Type	HB7130-2

Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3553 110304