

Garant
VBGT 110301, Grade: HU7310


Order data

Order number	261220 HU7310
GTIN	4045197696205
Item class	21G

Technical description

Feed f	0.05 - 0.5 mm/rev.
Chip breaker	AM
Cutting conditions	continuous
Corner radius	0.1 mm
Cutting depth a_p	0.1 - 4 mm
Main application	N
Cutting speed v_c main application	350 - 600 m/min
Grade	HU7310
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Coating	uncoated

ISO code indexable insert	VBGT 110301
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning