

Garant**VBGT 110302, Grade: HU7310**

Order data

Order number	261222 HU7310
GTIN	4045197696212
Item class	21G

Description

VBGT 110302 HU7310 Grade: HU7310
Chip breaker: AM
Tolerance: G
Cutting depth a_p : 0.1 - 4 mm
Feed f : 0.05 - 0.5 mm/rev.
Cutting speed v_c main application: 350 - 600 m/min

Technical description

Cutting depth a_p	0.1 - 4 mm
Corner radius	0.2 mm
Cutting speed v_c main application	350 - 600 m/min
Cutting conditions	continuous
Chip breaker	AM
Feed f	0.05 - 0.5 mm/rev.

Main application	N
Grade	HU7310
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	VBGT 110302
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning