

Garant
VB.T 160404, Grade: HB7310


Order data

Order number	261232 HB7310
GTIN	4045197696267
Item class	21G

Description

VB.T 160404 HB7310 Grade: HB7310
 Chip breaker: AM
 Tolerance: G
 Cutting depth a_p : 0.1 - 4 mm
 Feed f : 0.05 - 0.5 mm/rev.
 Cutting speed v_c main application: 350 - 600 m/min

Technical description

Main application	N
Cutting conditions	continuous
Feed f	0.05 - 0.5 mm/rev.
Cutting speed v_c main application	350 - 600 m/min
Corner radius	0.4 mm
Chip breaker	AM

Cutting depth a_p	0.1 - 4 mm
Grade	HB7310
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	VBGT 160404
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning