

**Garant****Screw-on toolholder, right-hand, Shank / insert size: 20/16mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 261308 20/16  |
| GTIN         | 4045197653772 |
| Item class   | 21T           |

**Technical description**

|                                 |                               |
|---------------------------------|-------------------------------|
| Head length L <sub>1</sub>      | 15 mm                         |
| ISO code toolholder             | SVHCR/L 2020K16               |
| Insert size                     | 16 mm                         |
| suitable indexable insert       | VC.. 1604..                   |
| Shank size                      | 20 mm                         |
| Pack of insert screws           | 269028 2                      |
| Shim screw                      | 269013 2                      |
| Shim                            | 269005 8                      |
| Functional width L <sub>4</sub> | 25 mm                         |
| Overall length L                | 125 mm                        |
| Standard                        | Works standard                |
| Application type                | right-hand                    |
| Through-coolant                 | no                            |
| Setting angle κ                 | 107.5 degrees                 |
| Application                     | External longitudinal turning |
| Application                     | External longitudinal turning |

|                 |            |
|-----------------|------------|
| Type of product | Boring bar |
|-----------------|------------|

---

### Accessories

|  |             |
|--|-------------|
| Shim screw Type 2  | 269013 2    |
| Set of insert screws Type 2  | 269028 2    |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15                            | 674248 TX15 |
| Shim Type 8  | 269005 8    |
| Set of insert screws Type 22   | 269028 22   |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500  |