



## Flange blank for geared scroll chuck, External Ø D: 260 mm



### Order data

Order number	317000 260
GTIN	4019208002996
Item class	33R

### Description

#### Version:

Cleanly cast, unmachined, shot blasted, large allowance.

#### Application:

Attachment of **chucks with recessed mount to DIN 6350 to spindle noses DIN 800**. The adaptor plate blank must be machined and fitted to the machine and chuck.

#### Material:

Cast iron

#### Suitable for :

**Three-jaw lathe chuck No. 310100; 310500**, four-jaw lathe chuck **No. 312000; 312500** and combi lathe chuck **No. 315630**.

suitable for chuck Ø: 250 mm

Collar Ø d<sub>2</sub>: 105 mm

Bore Ø d<sub>3</sub>: 50 mm

Height h<sub>1</sub>: 92 mm

Flange thickness h<sub>2</sub>: 25 mm

### Technical description

Bore Ø d <sub>3</sub>	50 mm
-----------------------	-------

suitable for chuck $\varnothing$	250 mm
External $\varnothing$ D	260 mm
Collar $\varnothing$ d <sub>2</sub>	105 mm
Height h <sub>1</sub>	92 mm
Flange thickness h <sub>2</sub>	25 mm
Type of product	Lathe chuck accessories