

Garant
Short drill chuck Form A, HSK-A 100, Clamping range: 0,5-16mm

Order data

Order number	307684 0,5-16
GTIN	4045197573452
Item class	31B

Description
Version:

- For clockwise and anticlockwise rotation.
- With RFID/Balluffchip bore.

Concentricity $\leq 20 \mu\text{m}$.

With through coolant feed up to max. 50 bar.

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Socket wrench No. 309890. Coolant tube No. 309880.

Technical description

Spare chuck key No. 627425	6 AF
Type	standard
Overhang dimension A	111 mm
Clamping range	0.5 - 16 mm
External \varnothing D	57 mm
Adapter	HSK-A 100
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-7

Arbor standard	DIN 69893-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 20 \mu\text{m}$
Type of product	Short drill chuck

Accessories

Hexagon screwdriver, with T-handle Hexagon 6 mm	627481 6
---	----------