

**ALZMETALL**  
we drive productivity

## Bench drill ALZTRONIC, maximum drill Ø in steel: 6 mm



### Order data

Order number	076560 6
GTIN	2050001755346
Item class	03P

### Description

#### Version:

High-speed, durable and precise bench drill.

- **AC motor 230 V, 50 Hz.**
- **Digital speed display.**
- **Stepless speed adjustment.**
- **Reversible.**
- **Swivelling spindle guard with electrical interlock.**
- **Mushroom-head pushbutton (latching) for EMERGENCY STOP.**
- **24-month warranty, 10-year spare part availability guarantee.**
- **Without drill chuck.**

With height-adjustable and swivelling drill head.

#### Attention:

German version. Order free UK adapter plug No. 08 1172\_GB.

#### Note:

Plates for other bench drills available on request.

Manufacturer's designation: ALZTRONIC 6

Power consumption: 540 W

maximum speed: 700 - 10000 rpm

Toolholder: B16

maximum machine tap Ø in steel: M6

Spindle stroke: 40 mm

## Technical description

Throat	200 mm
Machine baseplate height of usable area	240 mm
Spindle stroke	40 mm
maximum machine tap Ø in steel	M6
maximum drill Ø in steel	6 mm
Power consumption	540 W
Machine baseplate width of usable area	300 mm
Drill head height adjustment	Handwheel
Column Ø	50 mm
Manufacturer's designation	ALZTRONIC 6
maximum speed	700 - 10000 rpm
Distance spindle-base plate maximum	250 mm
Toolholder	B16
Weight	64 kg
Distance spindle-base plate minimum	110 mm
Feed	manual
T-slot nominal size	12 mm
Number of T-slots	2
T-slot pitch	80 mm