

Garant**VC.T 160408, Grade: HB7310**

Order data

Order number	261459 HB7310
GTIN	4045197672001
Item class	21G

Description

Technical description

Cutting conditions	continuous
Chip breaker	AM
Cutting depth a_p	0.1 - 4 mm
Corner radius	0.8 mm
Main application	N
Feed f	0.05 - 0.5 mm/rev.
Cutting speed v_c main application	350 - 600 m/min
Grade	HB7310
Finishing/roughing assignment	Finishing
Tool material	Carbide

ISO code indexable insert	VCGT 160408
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning