

ALZMETALL
we drive productivity

Bench drill ALZTRONIC, maximum drill Ø in steel: 9 mm



Order data

Order number	076560 9
GTIN	2050001755353
Item class	03P

Description

Version:

High-speed, durable and precise bench drill.

- **AC motor 230 V, 50 Hz.**
- **Digital speed display.**
- **Stepless speed adjustment.**
- **Reversible.**
- **Swivelling spindle guard with electrical interlock.**
- **Mushroom-head pushbutton (latching) for EMERGENCY STOP.**
- **24-month warranty, 10-year spare part availability guarantee.**
- **Without drill chuck.**

With height-adjustable and swivelling drill head.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

Plates for other bench drills available on request.

Manufacturer's designation: ALZTRONIC 9

Power consumption: 540 W

maximum speed: 390 - 6500 rpm

Toolholder: B16

maximum machine tap Ø in steel: M8

Spindle stroke: 40 mm

Technical description

Machine baseplate height of usable area	240 mm
Weight	64 kg
maximum speed	390 - 6500 rpm
Toolholder	B16
maximum machine tap Ø in steel	M8
Manufacturer's designation	ALZTRONIC 9
Throat	200 mm
Drill head height adjustment	Handwheel
Distance spindle-base plate minimum	110 mm
Distance spindle-base plate maximum	250 mm
maximum drill Ø in steel	9 mm
Spindle stroke	40 mm
Column Ø	50 mm
Feed	manual
Power consumption	540 W
Machine baseplate width of usable area	300 mm
T-slot nominal size	12 mm
Number of T-slots	2
T-slot pitch	80 mm