

SWISS TOOLS

**Toolholder axial, triple, right-hand, HSK-T 63, for toolholder square: 25mm****Order data**

Order number	318814 25
GTIN	2050001672667
Item class	36D

**Description****Version:**

With adjustable cooling nozzle with internal thread.

**Application:**

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

**Technical description**

Clamping length L <sub>1</sub>	58 mm
for toolholder square	25 mm
B	40 mm
Overhang dimension A	100 mm
External Ø D	102 mm
Adapter	HSK-T 63
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Pin vice

