

**AEG****Impact drill, Type: SB2E1100RV**

## Order data

Order number	075610 SB2E1100RV
GTIN	4002395294176
Item class	07A

## Description

**Version:**Powerful **impact drill**

- **Reversible.**
- **Safety shut-off.**
- **FIXTEC metal quick-change chuck.**
- **2-speed planetary gearbox for high torque and optimum adaptation to the material.**

Compact and powerful 1100 W impact drill with anti-vibration system (AVS).

**Advantage:**

Anti-vibration system.

**Supplied with:**

Metal quick-change chuck 1.5 - 13 mm, additional handle, drilling depth stop, transport case.

**Note:**

Suitable drill chucks can be found in Group 34.

## Technical description

maximum torque	60 Nm
maximum vibration to EN	13.7 m/s <sup>2</sup>

maximum twist drill size Ø in concrete	22 mm
Manufacturer's designation	SB2E1100RV
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 2nd speed	3200 min <sup>-1</sup>
Weight	2.9 kg
maximum twist drill size Ø in steel	13 mm
Power consumption	1100 W
maximum speed 1st speed	1000 min <sup>-1</sup>
maximum twist drill size Ø in wood	40 mm
Packaging	Carrying case
Power supply	Mains operated
Suitable for material	Concrete
Suitable for material	Stone
Suitable for material	Masonry
Type of product	Impact drill