



Heavy-duty chuck, SK 40, Ø D1: 20mm



Order data

Order number	300775 20
GTIN	4045197550866
Item class	32A

Description

Version:

- **Low friction due to needle bearings.**
- **Protected with anti-corrosion coating.**
- **Dust-tight and watertight.**
- **Very high clamping force prolongs tool life and improves surface quality.**
- **Flexible clamping range by means of collets.**

Application:

For clamping tools with plain shanks.

Supplied with:

Clamping nut.

Optional extras:

Pull studs No. 308600 – 308806.

Collets No. 309566 – 309570.

Technical description

Suitable C-hook (pin) spanner No. 628400	52 / 55
Collet outer Ø D	52 mm
Clamping Ø D ₁	20 mm
Overhang dimension A	90 mm
Clamping force up to	500 Nm
Adapter	SK 40

Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HPC
Type of product	Heavy-duty chuck

Accessories

Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Collet for heavy-duty chuck Nominal clamping Ø d 16 mm	309570 16
Collet for heavy-duty chuck Nominal clamping Ø d 18 mm	309570 18
Collet for heavy-duty chuck Nominal clamping Ø d 10 mm	309566 10
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Collet for heavy-duty chuck Nominal clamping Ø d 16 mm	309566 16
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull studForm A suitable for steep tapers 40	308600 40

Pull studsealed suitable for steep tapers 40	308635 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Collet for heavy-duty chuck Nominal clamping Ø d 6 mm	309566 6
Collet for heavy-duty chuck Nominal clamping Ø d 12 mm	309570 12
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Collet for heavy-duty chuck Nominal clamping Ø d 6 mm	309570 6
Collet for heavy-duty chuck Nominal clamping Ø d 10 mm	309570 10
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Collet for heavy-duty chuck Nominal clamping Ø d 12 mm	309566 12
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studForm B suitable for steep tapers 40	308640 40
Collet for heavy-duty chuck Nominal clamping Ø d 20 mm	309570 20
Collet for heavy-duty chuck Nominal clamping Ø d 25 mm	309570 25
Collet for heavy-duty chuck Nominal clamping Ø d 8 mm	309566 8
Collet for heavy-duty chuck Nominal clamping Ø d 8 mm	309570 8
Pull stud 45°sealed suitable for steep tapers 40	308765 40