

Garant
Threading insert set size 16, HB7010, Type: IR

Order data

Order number	271900 IR
GTIN	4045197370976
Item class	21J

Description
Content:

Full profile, metric 60°: No. 270756 size 1; 1.5; 1.75; 2; 2.5; 3

Partial profile, metric 60°: No. 270792 size 0.5-1.5; 1.75-3

Full profile, BSW 55°: No. 270824 size 14; 11

Technical description

Machining direction	right-hand
Tool material	Carbide
Thread type	M
Thread type	M-LH
Thread type	MF
Thread type	G
Thread type	BSW
Thread type	MF-LH
Thread type	G-LH
Thread type	BSW-LH
Grade	HB7010

Type of product

Indexable insert for thread turning

Accessories

Full profile insert 60°, internal, right-hand Pitch 1 mm	270756 1
Full profile insert 55°, internal, right-hand TPI 14	270824 14
Full profile insert 60°, internal, right-hand Pitch 1,5 mm	270756 1,5
Full profile insert 55°, internal, right-hand TPI 11	270824 11
Partial profile insert 60°, internal, right-hand Pitch 0,5-1,5 mm	270792 0,5-1,5
Full profile insert 60°, internal, right-hand Pitch 2 mm	270756 2
Full profile insert 60°, internal, right-hand Pitch 3 mm	270756 3
Full profile insert 60°, internal, right-hand Pitch 1,75 mm	270756 1,75
Full profile insert 60°, internal, right-hand Pitch 2,5 mm	270756 2,5
Partial profile insert 60°, internal, right-hand Pitch 1,75-3 mm	270792 1,75-3