

**ALZMETALL**  
 we drive productivity

**Bench drill ALZTRONIC, maximum drill Ø in steel: 14 mm**

**Order data**

Order number	076560 14
GTIN	2050001755377
Item class	03P

**Description**
**Version:**

High-speed, durable and precise bench drill.

- **AC motor 230 V, 50 Hz.**
- **Digital speed display.**
- **Stepless speed adjustment.**
- **Reversible.**
- **Swivelling spindle guard with electrical interlock.**
- **Mushroom-head pushbutton (latching) for EMERGENCY STOP.**
- **24-month warranty, 10-year spare part availability guarantee.**
- **Without drill chuck.**

With rigid and height-adjustable and swivelling machine table.

**Attention:**

German version. Order free UK adapter plug No. 08 1172\_GB.

**Note:**

Plates for other bench drills available on request.

Manufacturer's designation: ALZTRONIC 14

Power consumption: 540 W

maximum speed: 230 - 4000 rpm

Toolholder: MT2

maximum machine tap Ø in steel: M10

Spindle stroke: 80 mm

## Technical description

Throat	190 mm
Feed	manual
Distance spindle-base plate minimum	437 mm
Machine table height adjustment	hand crank
Weight	83 kg
Machine table length of usable area	300 mm
Distance spindle-machine table minimum	75 mm
maximum drill $\varnothing$ in steel	14 mm
Power consumption	540 W
maximum machine tap $\varnothing$ in steel	M10
Machine baseplate height of usable area	240 mm
maximum speed	230 - 4000 rpm
Toolholder	MT2
Spindle stroke	80 mm
Manufacturer's designation	ALZTRONIC 14
Machine baseplate width of usable area	300 mm
Distance spindle-base plate maximum	437 mm
Machine table width of usable area	240 mm
Column $\varnothing$	65 mm
Distance spindle-machine table maximum	357 mm
T-slot nominal size	12 mm
Number of T-slots	2
T-slot pitch	80 mm