



Battery charger, Type: 4PRO



Order data

Order number	081590 4PRO
GTIN	4013674014705
Item class	08C

Description

Version:

Microprocessor-controlled charging and servicing stations for battery cells with **individual channel monitoring** and battery fault detection. Status display for each charging slot, automatic charging switch-off, overload protection and **trickle charging**. Input voltage 100–240 V. With individually-selectable charging programmes for each charging slot, illuminated display and additional vehicle socket adaptor (12 V).

With LC display for detailed monitoring of the charging process. Additional USB-A charging output 5 V, 1000 mA, mains plug (100–240 V).

Attention:

German version. Order free UK adapter plug No. 08 1172_GB German version.

Interface: USB interface

maximum charging current: 1.8 A

Number of charging slots for USB: 1

Length: 119 mm

Width: 67 mm

Height: 31 mm

Technical description

Number of charging slots for USB	1
----------------------------------	---

Height	31 mm
Length	119 mm
Width	67 mm
maximum charging current	1.8 A
Interface	USB interface