



Battery charger, Type: 8PLUS



Order data

Order number	081590 8PLUS
GTIN	4013674207442
Item class	08C

Description

Version:

Microprocessor-controlled charging and servicing stations for battery cells with **individual channel monitoring** and battery fault detection. Status display for each charging slot, automatic charging switch-off, overload protection and **trickle charging**. Input voltage 100–240 V. With **refresh mode** for reactivating “tired” batteries. The Energy 8 plus automatically determines the optimum charging current for the battery and charges it at up to 1000mA in a quick-charge process.

Application:

NiMH/NiCd battery charging points: 1-4 × Micro AAA / Mignon AA or 1-3 × Baby C or 1-2 × Mono D / 9V block.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB

Interface: Digimatic interface

Nominal voltage: 100 - 240 V

maximum charging current: 1 A

Maximum number of charging points: 8

Length: 191 mm

Width: 172 mm

Height: 57 mm

Technical description

Maximum number of charging points	8
maximum charging current	1 A
Width	172 mm
Length	191 mm
Height	57 mm
Nominal voltage	100 - 240 V
Interface	Digimatic interface
Type of product	Battery charger