

HOLEX®
MT reducing adapter Form A, SK 50 short, MT internal: 3

Order data

| | |
|--------------|---------------|
| Order number | 301260 3 |
| GTIN | 4045197146007 |
| Item class | 32A |

Description
Version:

- **Ground internally and externally.**
- **With Balluffchip bore.**

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308810– 308830.

Arbor standard: DIN 69871

Arbor standard: ISO 7388-1

Shape: A

Balance quality G at rotational speed: G 6.3 at 15,000 rpm

Concentricity: $\leq 8 \mu\text{m}$

Overhang dimension A: 65 mm

External \varnothing D: 40 mm

Technical description

| | |
|--------------------------|-------------|
| Overhang dimension A | 65 mm |
| Morse taper internal | 3 |
| External \varnothing D | 40 mm |
| Adapter | SK 50 short |
| Arbor standard | DIN 69871 |
| Arbor standard | ISO 7388-1 |

| | |
|---------------------------------------|---------------------|
| Shape | A |
| Balance quality G at rotational speed | G 6.3 at 15,000 rpm |
| Concentricity | ≤ 8 µm |

Accessories

| | |
|---|-----------|
| Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50 | 308615 50 |
| Pull stud Form B suitable for steep tapers 50 | 308640 50 |
| Pull stud 60° sealed suitable for steep tapers 50 | 308785 50 |
| Pull stud, 18CrNiMo7 Form A suitable for steep tapers 50 | 308605 50 |
| Special pull stud with internal thread suitable for steep tapers 50 | 308740 50 |
| Torque insert for Pull studs to SO 7388 suitable for steep tapers 50 SK | 308812 50 |
| Pull stud 45° sealed suitable for steep tapers 50 | 308760 50 |
| Pull stud 45° sealed suitable for steep tapers 50 | 308765 50 |
| Pull stud stud sealed, form A suitable for steep tapers 50 | 308610 50 |
| Pull stud sealed suitable for steep tapers 50 | 308660 50 |
| Special pull stud with no internal thread sealed suitable for steep tapers 50 | 308720 50 |
| Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 50 SK | 308830 50 |
| Pull stud 90° sealed suitable for steep tapers 50 | 308790 50 |
| Pull stud 90° sealed suitable for steep tapers 50 | 308795 50 |
| Special pull stud with no internal thread sealed suitable for steep tapers 50 | 308700 50 |
| Pull stud sealed, form B suitable for steep tapers 50 | 308620 50 |
| Pull stud sealed, form B suitable for steep tapers 50 | 308650 50 |
| Pull stud Form A suitable for steep tapers 50 | 308600 50 |
| | 308820 50 |

Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 50 SK

Torque insert for Pull studs to DIN 69872 suitable for steep tapers 50 SK

308810 50