



Flow drilling set - flat including fluteless taps, for thread M: M5-M8



Order data

| | |
|--------------|---------------|
| Order number | 082726 M5-M8 |
| GTIN | 2050001740144 |
| Item class | 04D |

Description

Description:

The polygon contour of the carbide flow drill generates frictional heat which plasticises all types of metal materials. This allows closed apertures to be created in a variety of thicknesses of materials, without chips, in just a few seconds.

Advantage:

- **Large savings of time and costs compared to conventional processes (such as drawn-on nuts).**
- **Generates no chips or swarf; supersedes rivet nuts, weld nuts and press nuts.**
- **Solid basis for threads with high pull-out forces.**
- **For all popular material thicknesses and thread sizes (threads to DIN 13).**

Content:

1 each flowdrill and fluteless tap: Size M5; M6; M8

Note:

Other versions and sets for special applications (such as for thin sheet metal) available on request. **For suitable fluteless taps see items No. 139115 ff.**

Technical description

| | |
|-----------------|-------------|
| for thread M | M5-M8 |
| Type of product | Flow drills |

Accessories

| | |
|---|-----------|
| Flow drill - flat (no collar) for thread M M6 | 082735 M6 |
| Flow drill - flat (no collar) for thread M M8 | 082735 M8 |
| Flow drill - flat (no collar) for thread M M5 | 082735 M5 |