

Garant
MicroClamp – precision drill chuck, HSK-E 40 A = 46, Type: 0,2-3

Order data

Order number	308394 0,2-3
GTIN	4045197556875
Item class	31H

Description
Version:

- For clockwise and anticlockwise rotation.
- Radial run-out < 0.01 mm.
- Transmissible torque 7 Nm.
- Permissible speed: 60,000 rpm
- Permissible tightening torque 2 Nm.

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Coolant feed pipe No. 309880.

Machining strategy: HSC

Clamping range $\varnothing D_1$: 0.2 - 3.4 mm

External $\varnothing D$: 19 mm

$\varnothing D_2$: 12 mm

Spare chuck key: 627425 2

Technical description

Clamping range $\varnothing D_1$	0.2 - 3.4 mm
Spare chuck key	627425 2
$\varnothing D_2$	12 mm

External Ø D	19 mm
Adapter	HSK-E 40 A = 46
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	E
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Machining strategy	HSC
Type of product	Micro drill chuck

Accessories

Hexagon screwdriver with T-handle Hexagon 2 mm	627425 2
Hexagon screwdriver, with T-handle Hexagon 2 mm	627481 2