



## Flow drilling set - flat including fluteless taps, for thread M: M6-M10



### Order data

Order number	082726 M6-M10
GTIN	2050001740151
Item class	04D

### Description

#### Description:

The polygon contour of the carbide flow drill generates frictional heat which plasticises all types of metal materials. This allows closed apertures to be created in a variety of thicknesses of materials, without chips, in just a few seconds.

#### Advantage:

- **Large savings of time and costs compared to conventional processes (such as drawn-on nuts).**
- **Generates no chips or swarf; supersedes rivet nuts, weld nuts and press nuts.**
- **Solid basis for threads with high pull-out forces.**
- **For all popular material thicknesses and thread sizes (threads to DIN 13).**

#### Content:

1 each flowdrill and fluteless tap: Size M6; M8; M10

#### Note:

Other versions and sets for special applications (such as for thin sheet metal) available on request. **For suitable fluteless taps see items No. 139115 ff.**

### Technical description

for thread M	M6-M10
Type of product	Flow drills

---

## Accessories

Flow drill - flat (no collar) for thread M M8	082735 M8
Flow drill - flat (no collar) for thread M M10	082735 M10
Flow drill - flat (no collar) for thread M M6	082735 M6