

## Garant

### Pull stud, 18CrNiMo7 sealed, form B, without bore, suitable for steep tapers: 40



#### Order data

Order number	308615 40
GTIN	4045197554543
Item class	31Z

#### Description

##### Description:

The toolholder is securely pulled into the spindle by the spindle's clamping gripper using the pull stud. Pull studs come in different versions. They are an important link between the machine and tool. Stringent requirements apply for the accuracy, strength and reliability of pull studs.

##### Application:

- For tools with taper shanks see also **DIN 69871** and **JIS B 6339 (MAS-BT)**.
- In machining centres (machines with automatic tool changers).
- In NC machines (machines without automatic tool changers).

##### Note:

**Sealed** – with O-ring.

**ISO 7388-3** meets the old standard DIN 69872.

When installing the pull stud, cheque the correct tightening torque.

#### Technical description

suitable for taper arbors with colour code	SK 40
Head $\varnothing D_1$	19 mm
Angle A	15 degrees
Overall length L	54 mm
$L_1$	26 mm
Thread M	M16

maximum tightening torque	50 Nm
Collar Ø D	23 mm
suitable for steep tapers	40
Width across flats	19 mm
Hole characteristics	without bore
Pull stud standard	ISO 7388-3
Type of product	Pull Stud

---

## Accessories

Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308825 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40