



High-performance self-tightening drill chuck Spiro, Type: 100/12



Order data

Order number	341010 100/12
GTIN	4019208009407
Item class	39R

Description

Version:

High performance precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

Application:

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

Standard:

DIN 238

Technical description

Drill head length open	80 mm
Clamping range	0.5 - 10 mm
Drill chuck taper	B 12
Drill head length closed	91.5 mm
largest drill chuck taper \varnothing	12.056 mm
Type	100/12
External \varnothing	43 mm
Type of product	Drill chuck keyless

