



Combination face mill adapter Form ADB, BT 40 short, Spigot Ø d1: 40mm



Order data

Order number	302900 40
GTIN	4250122614029
Item class	36E

Description

Version:

Taper shank, spigots, and contact surfaces ground on collar.
All shanks burnished.

Application:

With drive key for face mills with longitudinal slot, e.g. DIN 841.

With drive ring for face mills with crosswise slot DIN 1880 and cutter heads DIN 1830.

Supplied with:

Drive key, face mill drive ring, and lock screw.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Special toggle spanner No. 309840.

Note:

Internal cooling available only with suitable tightening screw No. 309861.

Technical description

Suitable toggle spanner No. 309840	40
Overhang dimension A	60 mm
Spigot Ø d ₁	40 mm
Spare drive ring No. 309870	40
External Ø D	70 mm
Spare milling cutter lock screw No. 309860 / 309861	40
Adapter	BT 40 short

Standard	DIN 6358
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HPC
Type of product	Milling cutter spigot

Accessories

Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Toggle spanner for mandrel Ø 40 mm	309840 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Face mill drive ring for mandrel Ø 40 mm	309870 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Milling cutter lock screw for mandrel Ø 40 mm	309860 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40