



Short drill chuck Form A, SK 50, Clamping range: 2,5-16mm



Order data

Order number	301500 2,5-16
GTIN	4045197307651
Item class	37D

Description

Version:

For clockwise and anticlockwise rotation.
Burnished.

Supplied with:

Hexagon screwdriver with T-handle.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping range	2.5 - 16 mm
Spare chuck key No. 627425	SW6
Overhang dimension A	106.5 mm
External Ø D	56 mm
Adapter	SK 50
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 18,000 rpm
maximum tightening torque $M_{d\max}$	≤ 14 Nm
Type of product	Short drill chuck

Accessories

Pull studsealed, form A suitable for steep tapers 50	308610 50
Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull studForm B suitable for steep tapers 50	308640 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull studsealed, form B suitable for steep tapers 50	308650 50
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Pull studsealed suitable for steep tapers 50	308660 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull studForm A suitable for steep tapers 50	308600 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50