



Face mill arbor with cooling channel bore Form ADB, BT 50 A = 100, Spigot Ø d1: 40mm



Order data

Order number	303045 40
GTIN	4250122616344
Item class	36E

Description

Version:

Taper shank, spigots, and contact surfaces ground on collar.
All shanks burnished.

Supplied with:

Lock screw

Optional extras:

Pull studs (PS) No. 308760 – 308802. Special toggle spanner No. 309840.

Technical description

Overhang dimension A	100 mm
Suitable toggle spanner No. 309840	40
Spare milling cutter lock screw No. 309860 / 309861	40
Spigot Ø d ₁	40 mm
External Ø D	88 mm
Clamping Ø D ₁	40 mm
Adapter	BT 50 A = 100
Standard	DIN 6357
Arbor standard	ISO 7388-2

Arbor standard	JIS B6339
Shape	ADB
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Milling cutter lock screw for mandrel Ø 40 mm	309860 40
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Toggle spanner for mandrel Ø 40 mm	309840 40