



## Set of face drivers in a wooden box left-hand, Morse taper: 4



### Order data

Order number	327460 4
GTIN	4019208021256
Item class	35R

### Description

#### Version:

- Point angle 60°, clamping  $\varnothing$  8 - 80 mm.
- A pre-loaded axially adjustable disc spring pack compensates for differences in centre depths.
- The centre can be reground easily.

#### Application:

For mounting in the headstock taper of the lathe.

#### Supplied with:

1 base body No. 327520 (for clockwise and anticlockwise rotation),

1 centre No. 327660, 6 mm  $\varnothing$ , for driver head size 13 - 24,

1 centre No. 327660, 12 mm  $\varnothing$ , for driver head size 21 - 40,

4 driver heads for working range  $\varnothing$  13 – 100 mm (No. 327600 and 327610: Sizes 13 – 24, 21 – 40, 33 – 64; No. 327640 and 327650: Sizes 51 – 100).

Supplied in a wooden box with space for another 6 driver heads and 3 centres (for the complete working range  $\varnothing$  9 - 160 mm).

#### Note:

Counterpart to 321750 and 321770.

Working range  $\varnothing$ : 13 - 100 mm

Centre tip  $\varnothing$ : 6 / 12 mm

Weight: 4.3 kg

### Technical description

Weight	4.3 kg
Working range Ø	13 - 100 mm
Morse taper	4
Centre tip Ø	6 / 12 mm
Type of product	Face driver