



## Flow drill - standard (with collar), for thread M: M8



### Order data

Order number	082730 M8
GTIN	2050001740212
Item class	04D

### Description

#### Version:

Carbide flow drills for production of tapping holes preliminary to thread forming.

#### Description:

The high speed and frictional heat creates local high temperatures which plastify all types of metallic materials. This allows a bushing to be created in a variety of thicknesses of materials, without chips, in just a few seconds.

The polygon contour of the carbide flow drill generates frictional heat which plasticises all types of metal materials. This allows closed apertures to be created in a variety of thicknesses of materials, without chips, in just a few seconds.

#### Advantage:

- **Large savings of time and costs compared to conventional processes (such as drawn-on nuts).**
- **Generates no chips or swarf; supersedes rivet nuts, weld nuts and press nuts.**
- **Solid basis for threads with high pull-out forces.**
- **For all popular material thicknesses and thread sizes (threads to DIN 13).**

### Technical description

recommended drive power	1.3 kW
-------------------------	--------

maximum material thickness	3.3 mm
Tapping hole Ø	7.3 mm
recommended speed	2200 min <sup>-1</sup>
for thread M	M8
Shank Ø	8 mm
Type of product	Flow drills