

Garant**DNMG 150612, Grade: HB7120-1**

Order data

Order number	250864 HB7120-1
GTIN	4045197819833
Item class	21G

Description

DNMG 150612 HB7120-1 Grade: HB7120-1

Chip breaker: VG

Cutting depth a_p : 1.5 - 6 mmFeed f : 0.25 - 0.6 mm/rev.Cutting speed v_c main application: 70 - 240 m/min

Technical description

Feed f	0.25 - 0.6 mm/rev.
Chip breaker	VG
Grade	HB7120-1
Cutting depth a_p	1.5 - 6 mm
Cutting speed v_c main application	70 - 240 m/min
Cutting conditions	continuous
Corner radius	1.2 mm

Main application	M
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	DNMG 150612
Number of changes/inserts	4
Type of product	Indexable insert for turning