


Garant
KNUX 160405R, Grade: HB7120-1

Order data

Order number	251030 HB7120-1
GTIN	4045197819840
Item class	21G

Description

KNUX 160405R HB7120-1 Grade: HB7120-1

Chip breaker: VM

Chip diverter: 2.2 mm

Cutting depth a_p : 0.5 - 5 mm

Feed f : 0.2 - 0.5 mm/rev.

Cutting speed v_c main application: 80 - 260 m/min

Technical description

Cutting speed v_c main application	80 - 260 m/min
Feed f	0.2 - 0.5 mm/rev.
Main application	M
Cutting depth a_p	0.5 - 5 mm
Chip diverter	2.2 mm
Chip breaker	VM
Grade	HB7120-1
Corner radius	0.5 mm
Cutting conditions	continuous
Finishing/roughing assignment	Semi-roughing

Tool material	Carbide
Number of changes/inserts	2
ISO code indexable insert	KNUX 160405R
Type of product	Indexable insert for turning