

Garant**CNMG 160612, Grade: HB7120-1**

Order data

Order number	250336 HB7120-1
GTIN	4045197819697
Item class	21G

Description

CNMG 160612 HB7120-1 Grade: HB7120-1
Chip breaker: VG
Cutting depth a_p : 1.5 - 6 mm
Feed f : 0.25 - 0.6 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

Main application	M
Cutting conditions	continuous
Feed f	0.25 - 0.6 mm/rev.
Cutting speed v_c main application	70 - 240 m/min
Corner radius	1.2 mm
Cutting depth a_p	1.5 - 6 mm
Grade	HB7120-1

Chip breaker	VG
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	CNMG 160612
Number of changes/inserts	4
Type of product	Indexable insert for turning