

Garant
Shrink-fit chuck with cooling channel bores, SK 40 ultra short, Clamping range \varnothing D1: 25mm

Order data

Order number	302230 25
GTIN	4045197467690
Item class	31A

Description
Version:

- **High-temperature steel.**
- **Size 3 -5 for carbide, from size 6 for HSS and carbide.**
- **All shanks hard turned (for smooth running!).**
- **With RFID / Balluffchip bore.**

Ultra-short version for more stability and less vibration.

With **coolant hole bores** tapped for plugging.

Coolant hole bores at clamping \varnothing D1: 3, 4 and 5 mm cannot be plugged.

This results in a longer tool life and better surface qualities. Without length adjustment screw.

Application:

For clamping tools with parallel shank to h6 tolerance.

Suitable for inductive, contact, and hot-air shrink units.

Optional extras:

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

Note:

No length adjustment available.

Technical description

\varnothing D ₂	45 mm
------------------------------	-------

Clamping $\varnothing D_1$	25 mm
Overhang dimension A	75 mm
External $\varnothing D$	50 mm
Cooling channel bore	lockable
Adapter	SK 40 ultra short
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

Accessories

Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull studsealed suitable for steep tapers 40	308635 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull studForm B suitable for steep tapers 40	308640 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Screening plate for coilSU1 for clamping \varnothing 20-32 mm	354240 20-32
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40

Cooling unit Type CU1	354215 CU1
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Cooling adapter short4.5° for clamping Ø 22,1-32 mm	354235 22,1-32
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studsealed suitable for steep tapers 40	308660 40
Basic tool mountingfor SK for SK taper shank 40	354225 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Shrink-fit unit Type SU1	354210 SU1
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Cooling adapter long4.5° for clamping Ø 22,1-32 mm	354236 22,1-32
Pull studMazak, form A suitable for steep tapers 40M	308670 40M