



## HPH chuck, SK 40, Clamping range $\varnothing$ D1: 8mm



### Order data

Order number	302190 8
GTIN	
Item class	33W

### Description

#### Version:

Very high total rigidity due to optimised design. With Balluffchip bore. Suitable for minimum quantity lubrication.

Hydraulic clamping chuck, version **HPH** (High Performance Holder).

#### Advantage:

- **Very high transmitted torque, providing high process reliability.**
- **Ideal damping characteristics, resulting in optimum surface finishes, increased tool life and spindle protection.**

#### Application:

- **Especially for heavy-duty milling.**
- **For clamping tools with shank tolerance h6.**

#### Supplied with:

Hexagon cross-bar wrench.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806.

PS wrenches No. 308820 – 308835.

### Technical description

Overhang dimension A	75 mm
L <sub>1</sub>	56 mm
Clamping $\varnothing$ D <sub>1</sub>	8 mm
External $\varnothing$ D	50 mm

Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Type of product	Hydraulic clamping chuck