

Garant**WNMG 080408, Grade: HB7120-1**

Order data

Order number	252070 HB7120-1
GTIN	4045197820181
Item class	21G

Technical description

Cutting depth a_p	0.5 - 4 mm
Chip breaker	VM
Cutting conditions	continuous
Main application	M
Feed f	0.1 - 0.5 mm/rev.
Corner radius	0.8 mm
Cutting speed v_c main application	80 - 260 m/min
Grade	HB7120-1
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	WNMG 080408

Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning