

**Garant**
**Shrink-fit chuck, SK 40 A = 160, Clamping range  $\varnothing$  D1: 10mm**

**Order data**

Order number	302258 10
GTIN	4045197288028
Item class	31A

**Description**
**Version:**

- **High-temperature steel.**
- **Size 3 -5 for carbide, from size 6 for HSS and carbide.**
- **All shanks hard turned (for smooth running!).**
- **With RFID / Balluffchip bore.**

**Application:**

For clamping tools with parallel shank to h6 tolerance.  
Suitable for inductive, contact, and hot-air shrink units.

**Optional extras:**

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

**Technical description**

$\varnothing$ D <sub>2</sub>	24 mm
Overhang dimension A	160 mm
Clamping $\varnothing$ D <sub>1</sub>	10 mm
External $\varnothing$ D	32 mm
Adapter	SK 40 A = 160
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

## Accessories

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull studsealed suitable for steep tapers 40	308660 40
Shrink-fit chuck extension 4.5°with length adjustment screw Ø d / Ø D1 25/10 mm	302412 25/10
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull studsealed, form B suitable for steep tapers 40	308650 40
Screening plate for coilSU1 for clamping Ø 6-12 mm	354240 6-12
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 25/10 mm	302410 25/10
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studForm B suitable for steep tapers 40	308640 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40

Cooling adapter short 4.5° for clamping Ø 9,1-12 mm	354235 9,1-12
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Basic tool mounting for SK for SK taper shank 40	354225 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 25/10 mm	302416 25/10
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 32/10 mm	302416 32/10
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Cooling unit Type CU1	354215 CU1
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
Shrink-fit chuck extension 4.5° with length adjustment screw Ø d / Ø D1 32/10 mm	302412 32/10
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Shrink-fit chuck extension 4.5° without length adjustment screw, with through coolant holes Ø d / Ø D1 32/10 mm	302414 32/10
Pull stud sealed suitable for steep tapers 40	308635 40
Cooling adapter long 4.5° for clamping Ø 9,1-12 mm	354236 9,1-12
Shrink fit chuck extension 3°, vibration-damped Ø d / Ø D1 20/10 mm	302415 20/10
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull stud sealed, form A suitable for steep tapers 40	308610 40
Shrink-fit unit Type SU1	354210 SU1
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 32/10 mm	302410 32/10
	308700 40

Special pull stud with no internal threadsealed suitable for  
steep tapers 40

---