


**Garant**
**SNMG 120408, Grade: HB7120-1**


## Order data

Order number	251224 HB7120-1
GTIN	4045197819956
Item class	21G

## Description

SNMG 120408 HB7120-1 Corner radius: 0.8 mm  
 Grade: HB7120-1  
 Chip breaker: VM  
 Cutting depth  $a_p$ : 0.5 - 4 mm  
 Feed  $f$ : 0.1 - 0.4 mm/rev.  
 Cutting speed  $v_c$  main application: 80 - 260 m/min

## Technical description

Grade	HB7120-1
Feed $f$	0.1 - 0.4 mm/rev.
Cutting depth $a_p$	0.5 - 4 mm
Corner radius	0.8 mm
Chip breaker	VM
Cutting conditions	continuous
Cutting speed $v_c$ main application	80 - 260 m/min

Main application	M
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8
Type of product	Indexable insert for turning