

Garant**TNMG 160408, Grade: HB7120-1****Order data**

Order number	251544 HB7120-1
GTIN	4045197820068
Item class	21G

Description

TN.G 160408 HB7120-1 Grade: HB7120-1
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.5 - 5 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 80 - 260 m/min

Technical description

Grade	HB7120-1
Chip breaker	VM
Cutting speed v_c main application	80 - 260 m/min
Corner radius	0.8 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	0.5 - 5 mm
Main application	M

Cutting conditions	continuous
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	TNMG 160408
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning