


Garant**SNMG 190616, Grade: HB7120-1**

Order data

Order number	251336 HB7120-1
GTIN	4045197820013
Item class	21G

Description

SNMG 190616 HB7120-1 Corner radius: 1.6 mm
Grade: HB7120-1
Chip breaker: VG
Cutting depth a_p : 1.5 - 9 mm
Feed f : 0.25 - 0.8 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

Feed f	0.25 - 0.8 mm/rev.
Corner radius	1.6 mm
Main application	M
Chip breaker	VG
Cutting conditions	continuous
Cutting depth a_p	1.5 - 9 mm

Cutting speed v_c main application	70 - 240 m/min
Grade	HB7120-1
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMG 190616
Number of changes/inserts	8
Type of product	Indexable insert for turning