

Garant**DC.T 11T308, Grade: HB7120-1**

Order data

| | |
|--------------|-----------------|
| Order number | 260361 HB7120-1 |
| GTIN | 4045197817297 |
| Item class | 21G |

Description

DC.T 11T308 HB7120-1 Grade: HB7120-1
Chip breaker: VS
Tolerance: M
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 90 - 290 m/min

Technical description

| | |
|--------------------------------------|-------------------|
| Feed f | 0.1 - 0.3 mm/rev. |
| Main application | M |
| Chip breaker | VS |
| Cutting conditions | continuous |
| Grade | HB7120-1 |
| Cutting speed v_c main application | 90 - 290 m/min |

| | |
|-------------------------------|------------------------------|
| Corner radius | 0.8 mm |
| Cutting depth a_p | 0.2 - 1.5 mm |
| Finishing/roughing assignment | Finishing |
| Tool material | Carbide |
| ISO code indexable insert | DCMT 11T308 |
| Number of changes/inserts | 2 |
| Tolerance | M |
| Type of product | Indexable insert for turning |