

**Garant**
**TCMT 16T308, Grade: HB7120-1**

**Order data**

Order number	260958 HB7120-1
GTIN	4045197818737
Item class	21G

**Description**

TCMT 16T308 HB7120-1 Grade: HB7120-1  
 Chip breaker: VS  
 Cutting depth  $a_p$ : 0.2 - 1.5 mm  
 Feed  $f$ : 0.1 - 0.3 mm/rev.  
 Cutting speed  $v_c$  main application: 90 - 290 m/min

**Technical description**

Corner radius	0.8 mm
Cutting speed $v_c$ main application	90 - 290 m/min
Grade	HB7120-1
Cutting conditions	continuous
Main application	M
Feed $f$	0.1 - 0.3 mm/rev.
Chip breaker	VS
Cutting depth $a_p$	0.2 - 1.5 mm

Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TCMT 16T308
Number of changes/inserts	3
Type of product	Indexable insert for turning