

**Filament adhesive tape, Width×length (mm× m): 50X50****Order data**

Order number	083666 50X50
GTIN	2050001712370
Item class	08M

Description**Version:**

3M™ 8954 is made of PP with **high-tensile glass fibre-reinforcement (across and along)** with very high tear resistance and abrasion resistance. **Suitable for packaging hazardous goods for transport!**

Application:

For binding and securing, e.g. for securing pallets or products.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Technical description

Manufacturer's designation	8954
Colour	transparent
Width	50 mm
Thickness	0.13 mm

Length	50 m
Type of adhesive tape	single-sided
"Best before" date	12 mo
Stretch capability	10 %
Backing material	PP film
Liner present	no
Storage humidity	50 %
Tensile strength	13.5 N/mm
Adhesive	Synthetic rubbers
Special features	tear-resistant
Special features	moisture-resistant
Special features	abrasion resistant
Application	Bonding
Application	Binding
Application	Packing
Storage temperature	21 °C
temperature-resistant up to	60 °C
Adhesive strength on steel	0.7 N/mm
Type of product	Adhesive tape